

Self-aligning ball bearings 1317-K-M-C3

(Series 13..-K)

main dimensions to DIN 630, with tapered bore, taper 1:12

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	85 mm
D	180 mm
B	41 mm
D ₁	151,9 mm
d ₁	117,2 mm
Da max	166 mm
da max	114 mm
da min	99 mm
r _a max	2,5 mm
r _{min}	3 mm

m	5,32 kg	Mass
C _r	99000 N	Basic dynamic load rating, radial
C _{0r}	38000 N	Basic static load rating, radial
n _G	5800 1/min	Limiting speed
C _{ur}	2070 N	Fatigue limit load, radial
n _{gr}	4300 1/min	Reference speed
e	0,22	
Y ₁	2,88	
Y ₂	4,46	
Y ₀	3,02	
	H317	Designation, adapter sleeve

