

Barrel roller bearings 20324-MB (Series 203)

main dimensions to DIN 635-1

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	120 mm	
D	260 mm	
B	55 mm	
D ₁	222,3 mm	
D _{a max}	246 mm	
d _{a min}	134 mm	
r _{a max}	2,5 mm	
r _{min}	3 mm	
m	15,2 kg	Mass
C _r	490000 N	Basic dynamic load rating, radial
C _{0r}	630000 N	Basic static load rating, radial

Cur	52000 N	Fatigue limit load, radial
nG	2750 1/min	Limiting speed



