



Sealed spherical roller bearings

24126-BE-XL-2VSR (Series 241..-BE-2VSR)

lip seals on both sides, for continuous casting machines

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	130 mm
D	210 mm
B	80 mm
D ₁	196,1 mm
d ₂	143,1 mm
D _{a max}	199 mm
d _{a min}	141 mm
d _s	3,2 mm
r _s	6,5 mm
r _{a max}	2 mm
r _{min}	2 mm

m	11 kg	Mass
C _r	710000 N	Basic dynamic load rating, radial
C _{0r}	1050000 N	Basic static load rating, radial
C _{ur}	112000 N	Fatigue limit load, radial
n _G	700 1/min	Limiting speed
e	0,34	
Y ₁	1,98	
Y ₂	2,94	
Y ₀	1,93	



