

Deep groove ball bearings 6218-2Z (Series 62...-2Z)

main dimensions to DIN 625-1, gap seals on both sides

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue selection system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	90 mm
D	160 mm
B	30 mm
d ₁	112,3 mm
D ₂	143,4 mm
D _{a max}	149 mm
d _{a min}	101 mm
r _{a max}	2 mm
r _{min}	2 mm
m	2,26 kg Mass

C_r	102000 N	Basic dynamic load rating, radial
C_{0r}	74000 N	Basic static load rating, radial
C_{ur}	4500 N	Fatigue limit load, radial
n_G	5400 1/min	Limiting speed
$n_{\theta r}$	5100 1/min	Reference speed
f_0	14,6	Calculation factor



